PURITY C **Quell ST**




Experience unique quality

Specially developed for catering and vending sectors, the PURITY C Quell ST filter cartridges reduce carbonate hardness in drinking water and, therefore, reduce the danger of limescale deposits in equipment. In addition, the filter medium retains metal ions, such as lead or copper, and also reduces substances that can negatively affect taste and aroma (such as chlorine residues)

The benefits to you

- Limescale deposits and the associated machine breakdowns are reduced including additional service and repair costs
- The removal of unwanted taste and aroma elements in the filtrate (and also in the bypass water) for optimum quality of the end product
- One filter head concept for all cartridge versions in the PURITY C range with various head designs for individual requirements
- Simple to handle with rapid-change system including an innovative locking handle for reliable adjustment
- Integrated flush valve for easy operation and space-saving thanks to the water inlet and outlet on one side of the filter head





The Filter Service App is your ideal assistant. This unique, comprehensive tool helps determine the right type and size of filter for your precise needs. It provides detailed installation guidance for service engineers, calculates when cartridges will need replacing and has a wealth of other, innovative capabilities.

Download for free on App Store





Or visit https://professional.brita.net/app



Systematic filter technology

1 Pre-filtration

A pre-filter retains coarse particles.

Carbonate hardness reduction


The PURITY C Quell ST filter medium reduces carbonate hardness. As a result, unwanted limescale formation is prevented.

Activated carbon filtration

All of the water - including the bypass water - runs through an activated carbon filter, so substances that have an adverse effect on the taste and aroma are removed.

4 Fine filtration

At the end of the filtration process a fleece retains any fine particles.



The illustration serves as explanation of the filter technology. It is not to scale

Quality and safety

Optimum water quality

Outstanding and consistent water quality - free of unwanted taste and aroma elements.

Maximum product safety

For uninterrupted operation and safe use.

Operation after a softening unit

Usage after softening unit maintains approx. 70 % of its usual filter capacity.

Simple to use

Operation is simpler and easier than ever.

The food safety of BRITA Professional water filter products is tested and monitored by independent institutes.















*applies to all materials in contact with water

PURITY C Quell ST	C50	C150	C300	C500	C1100
Technology	decarbonisation				
PURITY C 0 - 70 % filter head with variable bypass					
Capacity¹ coffee/espresso/vending machines (at a carbonate hardness of 10 °dH/bypass setting of 40 %)	960 I	2,408	4,000 l	6,800 I	11,500 l
PURITY C 30 % filter head with fixed bypass					
Capacity ¹ with a carbonate hardness of 10 °dH	831 l	2,086 l	3,464 l	5,889	9,960 I
PURITY C 0 % filter head with fixed bypass					
Capacity ¹ with a carbonate hardness of 10 °dH	600 I	1,505 l	2,500 l	4,250 I	7,188 I
Max. operating pressure Water intake temperature	8.6 bar 4 - 30 °C				
Nominal flow (Pressure loss at nominal flow)	60 l/h (0.25 bar)			100 l/h (0.5 bar)	
Dimensions (W/D/H) with filter head	119/108/268 mm	117/104/419 mm	125/119/466 mm	144/144/557 mm	184/184/557 mm
Weight (dry/wet)	1.0/1.6 kg	1.8/2.8 kg	2.8/4.2 kg	4.6/6.9 kg	7.7/12.5 kg
Connections (input/output)	G 3/8" or John Guest 8 mm (JG 8)				
Operating position Operation	horizontal and vertical				
PURITY C Quell ST	Order number				
Filter cartridge	1002730 (Pack 1) 102831 (Pack 20)	102828 (Pack 1) 102829 (Pack 6)	102826 (Pack 1) 102827 (Pack 3)	1002045 (Pack 1)	1012446 (Pack 1)
Filter head 0 %² (G 3/8" JG 8)	1002949 (Pack 1)/297177 (Pack 20) 1002942 (Pack 1)/297176 (Pack 20)				
Filter head 30 %³ (G 3/8" JG 8)	1002952 (Pack 1)/297175 (Pack 20) 1002945 (Pack 1)/297174 (Pack 20)				
Filter head 0 - 70 %4 (G 3/8" JG 8)	1013637 (Pack 1)/1013634 (Pack 20) 1013636 (Pack 1)/1013633 (Pack 20)				
PURITY C Filter head set III 0 - 70 % (Filter head G 3/8", backflow preventer, CH test kit, wall mounting bracket ⁵)	1002937				
Accessories	Order number				
BRITA FlowMeter 10 - 100	1033041				
Hardness test kit (carbonate)	710800				
Backflow preventer (G 3/8" JG 8)	1000639 (Pack 3) 292069 (Pack 1)				

Appropriate hoses and hose sets from our comprehensive FlexConnect range as well as other accessories can be found in our price list.

¹The capacities given have been tested and calculated on the basis of normal application and machine conditions. Due to external influences (e.g. variations in raw water quality and/or machine type), deviations from these results can occur. ² For coolers ³ For coffee machines and vending machines

⁴ Can be used flexibly for all applications

⁵ Not suitable for cartridge size C1100

Only drinking water quality may be used as the water supply for BRITA water filters.

For more information please contact:

BRITA Water Filter Systems Ltd.

Explanatory notes

BRITA House | 9 Granville Way | Bicester | OX26 4JT | United Kingdom Tel.: +44 844 742-4990 | Fax: +44 186 936-5962 clientservices@brita.co.uk | www.brita.co.uk

BRITA Water Filter Systems Distributors Pty Ltd

Suite 2, Level 9, 123 Epping Road | Macquarie Park, NSW, 2113 | Australia Tel.: +61 1300 955-021 | NZ: 0800 482-008 professional@brita.com.au | www.brita.com.au

Headquaters: BRITA SE

Heinz-Hankammer-Straße 1 | 65232 Taunusstein | Germany Tel.: +49 6128 746-0 | Fax: +49 6128 746-5033 info@brita.net | www.brita.net

BRITA Recycling Program

the BRITA corporate philosophy. As early as 1992, we established a recycling programme for our filter



brita.co.uk/recycling-professional